

ClickShare CX-50

Interact, discuss, collaborate with remote participants in superior AV quality driving multi-content sharing



- Full BYOD support
- Remote collaboration (full HD)
- Full interactivity and moderation
- Triple agnostic: works with any device, and UC technology and any brand of AV USB-peripheral
- HDMI input cable
- Enhanced security
- Connected and cloud managed
- Delivered with 2 Conferencing Buttons
- Collaborate with Conferencing Button or Collaboration App

ClickShare CX-50 brings superior wireless conferencing to meeting participants: local, guest or remote. Start a boardroom meeting from your device, use your preferred conference tool. Automatically connect wirelessly to the room cameras, microphones, soundbars for a more immersive, supreme AV quality meeting. Conference, collaborate, click in less than 7 seconds.

Bring your own meeting and decide how you want to collaborate. Use the ClickShare Wireless Conferencing Button and the ClickShare Collaboration App for pc and Mac or mobile devices for intuitive and uniform user experiences. Make meetings richer with interactivity features like signage, annotation, blackboarding, moderation, local view of the room display and touch back support.

A set of IT friendly features makes ClickShare Conference a perfect fit to any enterprise environment. ClickShare Conference, excelling in enhanced security, seamlessly integrates in any IT- network. With the XMS Cloud Management Platform you enjoy easy management of units, intuitive user experiences and clear analytics to drive your digital workplace.

PRODUCT SPECIFICATIONS**CLICKSHARE CX-50**

ClickShare Base Unit dimensions	
Dimensions (HxWxD)	39mm x 200mm x 202mm
Power supply	Standard 110/220 V AC plug
Power consumption	Operational: 50W (max) Standby:
Weight	900 gr
General specifications	
Operating system	Windows 8/8.1/10, macOS 10.13 and higher. Android v9 and higher (ClickShare app). iOS 12 and higher (ClickShare app)
Video outputs	4K UHD (3840*2160) @ 30Hz. HDMI 1.4b
Video inputs	1920x1080 @30Hz. HDMI 1.4b
Audio output	USB, SPDIF, jack, HDMI
USB	3 X USB-A, 1 X USB-C
Clickshare Buttons	2
ClickShare App	Desktop & Mobile
Native protocols	Aiplay, Google Cast, Miracast
Noise Level	Max. 25dBA @ 0-30°C Max. 30dBA @ 30-40°C
Authentication protocol	WPA2-PSK in stand alone mode WPA2-PSK or IEEE 802.1X using the ClickShare Button in network integration mode
Wireless transmission protocol	IEEE 802.11 a/g/n/ac and IEEE 802.15.1
Reach	Adjustable with signal strength modulation; max. 30m (100 ft) between ClickShare Button and ClickShare Base Unit Frequency band 2.4 GHz and 5 GHz (DFS)
Frequency band	2.4 GHz and 5 GHz (DFS channels supported in select number of countries)
Connections	1x Ethernet LAN 1Gbit 1x USB Type-C 2.0 (back); 2x USB Type A 2.0 (back); 1x USB Type A 2.0 (front) Audio analog line out on mini jack socket (3.5mm), digital S/PDIF
Temperature range	Operating: 0°C to +40°C (+32°F to +104°F) Max: 35°C (95°F) at 3000m Storage: -20°C to +60°C (-4°F to +140°F)
Humidity	Storage: 0 to 90% relative humidity, non-condensing Operation: 0 to 85% relative humidity, non-condensing
Anti-theft system	Kensington lock
Certifications	FCC/CE
Touch screen support & Interactivity	Yes
Room Dock (peripheral support)	High quality
Local view & moderation	High quality
Network connection	LAN & WiFi (dual)
Management and reporting	Yes
Warranty	5 years coverage via SmartCare
*	* depends on configuration

Last updated: 18 Nov 2019

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.